



SCOPE OF ACCREDITATION TO ISO/IEC 17025:2017
& ANSI/NCSL Z540-1-1994

ENDRESS+HAUSER, INC.
 14525 Kirby Road
 Pearland, TX 77047
 Benjamin Scher Phone: 888 363 7377

CALIBRATION

Valid To: September 30, 2026

Certificate Number: 3041.01

In recognition of the successful completion of the A2LA evaluation process (including an assessment of the organization's compliance with A2LA's Calibration Program Requirements), accreditation is granted to this laboratory to perform the following calibrations^{1, 6}:

I. Electrical – DC/Low Frequency³

Parameter/Equipment	Range	CMC ^{2, 4, 5} (±)	Comments
DC Current – Measure	(0 to 100) μ A 100 μ A to 1 mA (1 to 10) mA (10 to 100) mA 100 mA to 1 A (1 to 3) A	0.058 % + 0.025 % of rng 0.058 % + 0.006 % of rng 0.058 % + 0.020 % of rng 0.058 % + 0.005 % of rng 0.12 % + 0.010 % of rng 0.17 % + 0.020 % of rng	Agilent 34410A / Keysight 34465A
	(0 to 50) mA	0.012 % + 1 μ A	
DC Current – Generate	(0 to 100) mA	0.0059 % + 1 μ A	Martel 3001 / Fluke 7526A
DC Voltage – Measure	(0 to 100) mV (0 to 1) V (0 to 10) V (0 to 100) V (100 to 1000) V	0.0059 % + 0.0035 % of rng 0.004 % + 0.0007 % of rng 0.0035 % + 0.0005 % of rng 0.0047 % + 0.0006 % of rng 0.0047 % + 0.0006 % of rng	Agilent 34410A / Keysight 34465A
	DC Voltage – Generate	(0 to 100) mV (0 to 1) V (0 to 10) V (0 to 100) V	

Parameter/Equipment	Range	CMC ^{2,4,5} (±)	Comments
Thermocouple Output– (Electrical Simulation of Thermocouples)	(-10 to 75) mV	0.0038 % + 3 μV	Martel 3001 / Fluke 7526A
Type E	(-250 to 1000) °C	0.3 °C	Martel 3001 / Fluke 7526A
Type J	(-210 to 1200) °C	0.5 °C	
Type K	(-200 to 1372) °C	0.6 °C	
Type T	(-250 to 400) °C	0.7 °C	
Thermocouple Input	(-10 to 75) mV	0.0038 % + 3 μV	Martel 3001 / Fluke 7526A
Resistance – Measure	(0 to 400) Ω 0 Ω to 4 kΩ	0.0041 % + 0.004 Ω 0.0041 % + 0.04 Ω	Martel 3001/ Fluke 7526A
Resistance – Generate (Electrical Simulation of RTD)	(5 to 400) Ω 5 Ω to 4 kΩ	0.026 Ω 0.40 Ω	Martel 3001/ Fluke 7526A
Pt 385, 100 Ω	(-200 to -80) °C (-80 to 0) °C (0 to 100) °C (100 to 300) °C (300 to 400) °C (400 to 630) °C (630 to 800) °C	0.06 °C 0.07 °C 0.07 °C 0.07 °C 0.07 °C 0.08 °C 0.08 °C	Martel 3001/ Fluke 7526A

II. Fluid Quantities

Parameter/Equipment	Range	CMC ^{2,4} (±)	Comments
Flowrate – Liquids			
Flow Rig FCP8.2US:			
Mass	(0.02 to 10) kg/s	0.043 %	Gravimetric flow rig
Volumetric	(0.02 to 10) l/s	0.045 %	
Mass	(0.02 to 27.8) kg/s	0.047 %	Gravimetric flow rig w/ Coriolis reference standards
Volumetric	(0.02 to 27.8) l/s	0.049 %	

Parameter/Equipment	Range	CMC ^{2,4} (±)	Comments
Flowrate – Liquids (cont)			
Flow Rig FCP25.3US:			
Mass	(0.5 to 12) kg/s	0.014 %	Gravimetric flow rig
Volumetric	(0.5 to 12) l/s	0.018 %	
Mass	(0.5 to 5) kg/s	0.042 %	Gravimetric flow rig w/ single bank of Coriolis reference standards
Volumetric	(0.5 to 5) l/s	0.044 %	
Mass	(5 to 130) kg/s	0.032 %	Gravimetric flow rig w/ multiple banks of Coriolis reference standards
Volumetric	(5 to 130) l/s	0.035 %	
Flow Rig FCP1.4US:			
Mass	(50 to 1500) g/min	0.042 %	Gravimetric flow rig w/ single bank of Coriolis reference standards
Volumetric	(50 to 1500) ml/min	0.044 %	

III. Mechanical

Parameter/Equipment	Range	CMC ² (±)	Comments
Pressure – Gauges & Transducers			
Gauge, Pneumatic	(0.13 to 165) psia (0.13 to 315) psia (0.13 to 765) psia (atm to 7.5) psig (atm to 15) psig (atm to 30) psig (atm to 60) psig (atm to 165) psig	0.013 % FS 0.013 % FS 0.013 % FS 0.013 % FS 0.013 % FS 0.013 % FS 0.013 % FS 0.013 % FS	Mensor CPC6000
Differential	(-14.7 to 500) psid	0.013 % FS	

IV. Thermodynamic

Parameter/Equipment	Range	CMC ^{2,7} (±)	Comments
Temperature – Measuring Equipment	(-40 to 100) °C (100 to 300) °C	0.025 °C 0.040 °C	Liquid bath w/SPRT & thermometer

V. Time & Frequency

Parameter/Equipment	Range	CMC ^{2,4,7} (±)	Comments
Frequency – Measure	10 Hz to 10 kHz (3 to 5) Hz (5 to 10) Hz (10 to 40) Hz 40 Hz to 300 kHz	0.0015 % 0.081 % 0.047 % 0.023 % 0.0082 %	Agilent 53131A Agilent 34410A / Keysight 34465A
Frequency – Measuring Equipment	10 Hz to 20 MHz	0.0023 % + 3 pHz	Agilent 33220A

¹ This laboratory offers commercial calibration service.

² Calibration and Measurement Capability Uncertainty (CMC) is the smallest uncertainty of measurement that a laboratory can achieve within its scope of accreditation when performing more or less routine calibrations of nearly ideal measurement standards or nearly ideal measuring equipment. CMCs represent expanded uncertainties expressed at approximately the 95 % level of confidence, usually using a coverage factor of $k = 2$. The actual measurement uncertainty of a specific calibration performed by the laboratory may be greater than the CMC due to the behavior of the customer’s device and to influences from the circumstances of the specific calibration.

³ It is common practice for the laboratory to perform calibration of electrical parameters associated with one of the above calibration methods as it is related to the process instrument. In many cases, the calibration of electrical parameters (i.e., voltage, current, frequency, etc.) is required to determine the value of a flow, pressure, or temperature variable in a system where a transmitter or remote indicating device is one component in the whole system being calibrated. It is not the practice of the laboratory to perform calibration of electrical parameters on electrical equipment (i.e., digital multi-meters, oscilloscopes, etc.) for customers and is not intended to be perceived that way in the scope of accreditation.

⁴ In the statement of CMC, percentages are to be read as percentage of reading, unless otherwise indicated.

⁵The stated measured values are determined using the indicated instrument (see Comments). This capability is suitable for the calibration of the devices intended to measure or generate the measured value in the ranges indicated. CMC's are expressed as either a specific value that covers the full range or as a percent or fraction of the reading plus a fixed floor specification.

⁶ This scope meets A2LA's *P112 Flexible Scope Policy*.

⁷ The type of instrument or material being calibrated is defined by the parameter. This indicates the laboratory is capable of calibrating instruments that measure or generate the values in the ranges indicated for the listed measurement parameter.



Accredited Laboratory

A2LA has accredited

ENDRESS+HAUSER, INC.

Pearland, TX

for technical competence in the field of

Calibration

This laboratory is accredited in accordance with the recognized International Standard ISO/IEC 17025:2017 *General requirements for the competence of testing and calibration laboratories*. This laboratory also meets the requirements of ANSI/NCSL Z540-1-1994 and R205 – Specific Requirements: Calibration Laboratory Accreditation Program. This accreditation demonstrates technical competence for a defined scope and the operation of a laboratory quality management system (refer to joint ISO-ILAC-IAF Communiqué dated April 2017).



Presented this 7th day of October 2024.

A blue ink signature of Trace McInturff, written in a cursive style.

Mr. Trace McInturff, Vice President, Accreditation Services
For the Accreditation Council
Certificate Number 3041.01
Valid to September 30, 2026

For the calibrations to which this accreditation applies, please refer to the laboratory's Calibration Scope of Accreditation.